

# Apparel Sortation Case Study

## Casual Male XL-Direct to Consumer Sorter



- ▶ Single Split-tray model #ESF 46SS
- ▶ Units per hour:14,400
- ▶ Number of destinations:238
- ▶ Number of induction areas:2
- ▶ 7 manual induction stations
- ▶ Camera Based barcode scanner and hand scan station
- ▶ Type of Discharges:
  - \* Direct to tote for lot sorting  
70 direct to tote destinations
  - \* Double/Double chamber packing chutes for final order sorting  
168 distinct sorting chambers  
168 pack out chambers

CASUAL | MALE XL

The Casual Male XL direct to consumer sorter is unique in that it operates as (2) virtual sorters. One side of the sorter discharges items direct into a tote for lot sorting. The opposite side of the sorter discharges product direct to a packing chute which is used for final order sorting.



**EuroSort**

High Speed Sortation Solutions

## Technical Details



- ❑ Double/Double chamber packing chute for order sort



- ❑ Lot side discharge direct into tote



- ❑ Manual induction stations



- ❑ Tote delivery system from lot side to final order sort



High Speed Sortation Solutions

EuroSort Inc.  
55 New Plant Ct.  
Owings Mills, MD 21117  
Phone: (410) 363-6345  
Fax: (410) 363-6556  
[www.eurosort.com](http://www.eurosort.com)